# 760178897 | 360-A-CPANEL



#### Angled Panel Cover Cool Gray

### Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America		
Portfolio	SYSTIMAX®		
Product Type	Cover		

# General Specifications

Application	For angled panel
Color	Cool gray
Rack Type	EIA 19 in

#### Dimensions

Height	2.286 mm   0.09 in
Width	328.676 mm   12.94 in
Depth	97.028 mm   3.82 in

### Material Specifications

# **Environmental Specifications**

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	UL   cUL

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 8, 2023



# 760178897 | 360-A-CPANEL

# Regulatory Compliance/Certifications

Agency
--------

#### Classification

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 8, 2023

