

# RMG-24MPODQ4

---

RMG Fiber Optic Module, 24-fiber, MPO-LC, Multimode, OM3, aqua

## Product Classification

<b>Regional Availability</b>	Asia   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber module
<b>Product Series</b>	RMG

## General Specifications

<b>Functionality</b>	Breakout
<b>Application</b>	For use with RMG panels
<b>Adapter Color</b>	Aqua
<b>Adapters, quantity, front</b>	6
<b>Adapters, quantity, rear</b>	2
<b>Body Style</b>	Quad   Straight orientation
<b>Color, front</b>	Black
<b>Color, housing</b>	Black
<b>Color, rear</b>	Black
<b>Interface, front</b>	LC/UPC
<b>Interface, rear</b>	MPO
<b>Interface Feature, rear</b>	Standard
<b>Total Ports, quantity, front</b>	24

## Dimensions

<b>Height</b>	28.45 mm   1.12 in
<b>Width</b>	129.03 mm   5.08 in
<b>Depth</b>	115.82 mm   4.56 in

## Optical Specifications

<b>Fiber Mode</b>	Multimode
<b>Fiber Type</b>	OM3

# RMG-24MPODQ4

---

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Bag   Carton

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant

