



## Shielded Panel Frame, UCP Quick-Fit, 1U, Black

- Preferred replacement when used with MRJ21 and ACO applications

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Patch panel   |
| <b>Product Series</b>        | SL Series   |

## General Specifications

|                          |                                    |
|--------------------------|------------------------------------|
| <b>Application</b>       | For use with UCP Quick Fit modules |
| <b>Color</b>             | Black                              |
| <b>Modules, quantity</b> | 4                                  |
| <b>Panel Style</b>       | Straight                           |
| <b>Rack Type</b>         | EIA 19 in                          |
| <b>Rack Units</b>        | 1                                  |

## Dimensions

|                                     |                     |
|-------------------------------------|---------------------|
| <b>Height</b>                       | 43.8 mm   1.724 in  |
| <b>Width</b>                        | 482.6 mm   19 in    |
| <b>Depth, with cable management</b> | 240.5 mm   9.469 in |

## Material Specifications

|                      |                                    |
|----------------------|------------------------------------|
| <b>Material Type</b> | Galvanised and powder-coated steel |
|----------------------|------------------------------------|

## Environmental Specifications

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Operating Temperature</b> | -10 °C to +60 °C (+14 °F to +140 °F) |
| <b>Storage Temperature</b>   | -40 °C to +70 °C (-40 °F to +158 °F) |
| <b>Relative Humidity</b>     | Up to 95%, non-condensing            |
| <b>Flammability Rating</b>   | UL 94 V-0                            |

# 760239400 | CPP-QF-1U-E

---

**Safety Standard**

UL | cUL

## Packaging and Weights

**Packaging quantity**

1

## Regulatory Compliance/Certifications

**Agency**

**Classification**

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

