



## SLX Jack Color Cap with Dust Cover, Light Almond (50 ea/pkg)

- Fits on all SLX jacks

### Product Classification

|                              |                                                                     |
|------------------------------|---------------------------------------------------------------------|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®                                                          |
| <b>Product Type</b>          | Color Cap                                                           |

### General Specifications

|                                   |              |
|-----------------------------------|--------------|
| <b>Color</b>                      | Light almond |
| <b>Integrated Dust Cover Type</b> | Hinged       |

### Dimensions

|               |                     |
|---------------|---------------------|
| <b>Height</b> | 16.13 mm   0.635 in |
| <b>Width</b>  | 14.43 mm   0.568 in |
| <b>Depth</b>  | 8.25 mm   0.325 in  |

### Material Specifications

|                      |                                             |
|----------------------|---------------------------------------------|
| <b>Material Type</b> | High-impact, flame retardant, thermoplastic |
|----------------------|---------------------------------------------|

### Environmental Specifications

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Operating Temperature</b> | -10 °C to +60 °C (+14 °F to +140 °F) |
| <b>Storage Temperature</b>   | -40 °C to +70 °C (-40 °F to +158 °F) |

### Packaging and Weights

|                           |    |
|---------------------------|----|
| <b>Packaging quantity</b> | 50 |
|---------------------------|----|

### Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>                                                                                                          |
|---------------|--------------------------------------------------------------------------------------------------------------------------------|
| CHINA-ROHS    | Below maximum concentration value                                                                                              |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |

ROHS Compliant

UK-ROHS Compliant

