# 68MCLICK



## Miniature Click-on Hanger for 6-8 mm cable

## **Product Classification**

Product Type Hanger kit

Ordering Note CommScope® non-standard product

General Specifications

Cables per Hanger 2

**Color** Black

Hanger TypeClick-on hangerMountingM8 through hole

**Dimensions** 

Maximum Stack Height 3

 Height
 38.1 mm | 1.5 in

 Width
 16 mm | 0.63 in

 Length
 35.1 mm | 1.382 in

**Compatible Cable Diameter Range** 5.8–8.1 mm

Compatible Diameter, maximum8.1 mm | 0.319 inCompatible Diameter, minimum5.8 mm | 0.228 in

Nominal Size 1/4 in

**Electrical Specifications** 

Return Loss Effect, maximum 0.1 dB

DTF Effect, maximum 0.1 dB

Material Specifications

Material Type Engineered plastic

Mechanical Specifications

COMMSC PE®

# 68MCLICK

#### **Vibration Survival**

≥4 hours at resonant frequency

## **Environmental Specifications**

**Operating Temperature**  $-40 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F}$ )

**Environmental Strength Capability**Double cable weight

**UV Resistance, minimum with no degradation** ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

 Height, packed
 30.4 cm | 11.969 in

 Width, packed
 27.9 cm | 10.984 in

 Length, packed
 2.5 cm | 0.984 in

Packaging quantity 10

**Weight, gross** 0.09 kg | 0.198 lb

## Regulatory Compliance/Certifications

### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



### \* Footnotes

Maximum Stack Height Fiber, Hybrid, Power

