

# 912MCLICK

---



## Miniature Click-on Hanger for 9–12 mm cable

### Product Classification

<b>Product Type</b>	Hanger kit
<b>Ordering Note</b>	CommScope® standard product (Global)

### General Specifications

<b>Cables per Hanger</b>	2
<b>Color</b>	Black
<b>Hanger Type</b>	Click-on hanger
<b>Mounting</b>	M8 through hole

### Dimensions

<b>Maximum Stack Height</b>	3
<b>Height</b>	38.1 mm   1.5 in
<b>Width</b>	20.1 mm   0.791 in
<b>Length</b>	42.9 mm   1.689 in
<b>Compatible Cable Diameter Range</b>	9–12 mm
<b>Compatible Diameter, maximum</b>	12 mm   0.472 in
<b>Compatible Diameter, minimum</b>	9 mm   0.354 in
<b>Nominal Size</b>	1/4 in   3/8 in

### Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

### Material Specifications

<b>Material Type</b>	Engineered plastic
----------------------	--------------------

### Mechanical Specifications

<b>Vibration Survival</b>	≥4 hours at resonant frequency
---------------------------	--------------------------------

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Environmental Strength Capability</b>	Double cable weight
<b>UV Resistance, minimum with no degradation</b>	≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

<b>Height, packed</b>	15.2 cm   5.984 in
<b>Width, packed</b>	20.3 cm   7.992 in
<b>Length, packed</b>	2.5 cm   0.984 in
<b>Packaging quantity</b>	10
<b>Weight, gross</b>	0.13 kg   0.287 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power