



ERA® Wireless Communications Switch Subrack, 4 U -48Vdc

This unit does not support CAT6A powered access points.

Product Classification

| | |
|----------------------|---------|
| Product Type | Subrack |
| Product Brand | ERA® |

General Specifications

| | |
|----------------------------------|--|
| Mounting | Rack |
| Note | Detailed Product Specifications are available. Please contact your local CommScope representative. |
| Rack Type | EIA 19 in |
| Slots Available, quantity | 19 |

Dimensions

| | |
|---------------|--------------------|
| Height | 177 mm 6.969 in |
| Width | 482 mm 18.976 in |
| Depth | 450 mm 17.717 in |

Packaging and Weights

| | |
|-----------------------|-----------------------|
| Height, packed | 522 mm 20.551 in |
| Width, packed | 585 mm 23.032 in |
| Depth, packed | 185 mm 7.283 in |
| Included | Fan filter Fan tray |
| Weight, net | 10.8 kg 23.81 lb |

Regulatory Compliance/Certifications

| Agency | Classification |
|--------|----------------|
|--------|----------------|

CHINA-ROHS

Above maximum concentration value

ROHS

Compliant/Exempted

