



LSA-PLUS® Comprotect Overtoltage Plug, 2/1, CP OD180A1

## Product Classification

<b>Regional Availability</b>	Asia   EMEA
<b>Product Type</b>	Overtoltage plug
<b>Product Brand</b>	LSA-PLUS®

## General Specifications

<b>Transmission Standards</b>	DIN EN 60068-2-1   DIN EN 60068-2-2/3   DIN EN 60068-2-6   ITU-T K.12
-------------------------------	---

## Dimensions

<b>Height</b>	12.7 mm   0.5 in
<b>Width</b>	9.652 mm   0.38 in
<b>Length</b>	38.608 mm   1.52 in

## Electrical Specifications

<b>Capacitance</b>	50 pF
<b>Current Rating, maximum</b>	0.06 A
<b>dc Resistance, maximum</b>	1 ohm
<b>Dielectric Strength</b>	1.8 kV
<b>Safety Voltage Rating</b>	180 V

## Environmental Specifications

<b>Operating Temperature</b>	-20 °C to +60 °C (-4 °F to +140 °F)
<b>Storage Temperature</b>	-40 °C to +80 °C (-40 °F to +176 °F)
<b>Environmental Space</b>	Indoor

## Packaging and Weights

<b>Packaging quantity</b>	10
<b>Packaging Type</b>	Bag   Box

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

