

# FBR-COIL-S

---



HELIAX® Excess Discrete Fiber Coiling Reel, accommodates 16ft (5m) of excess 7mm fiber, weights 5lbs fully populated, stackable, PIM free

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Outdoor storage coil
<b>Product Brand</b>	HELIAX®

## General Specifications

<b>Color</b>	Black
<b>Mounting</b>	Angle iron   Pipe, 44–88.9 mm (1.75–3.5 in) OD

## Dimensions

<b>Height</b>	203.2 mm   8 in
<b>Width</b>	139.7 mm   5.5 in
<b>Depth</b>	50.8 mm   2 in

## Material Specifications

<b>Material Type</b>	Plastic
----------------------	---------

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +75 °C (-40 °F to +167 °F)
<b>Environmental Space</b>	Indoor   Outdoor

## Packaging and Weights

<b>Included</b>	Mounting hardware
<b>Weight, net</b>	0.454 kg   1 lb

## Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

# FBR-COIL-S

---

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

