



AMP STACK™ III Connector Splice Kit, dry, 25-pair

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Connector kit
Product Brand	AMP STACK™
Product Series	AMP STACK
Ordering Note	Minimum order quantity, 120 parts

General Specifications

Color	Gold ivory Transparent
Connector Sealant	Dry
Connector Splicing Type	Straight (In-line)
Pairs, quantity	25

Dimensions

Compatible Insulated Conductor Diameter, maximum	1.65 mm 0.065 in
Compatible Conductor Gauge, solid	28–20 AWG

Material Specifications

Contact Base Material	Phosphor Bronze
Contact Plating Material	Tin
Material Type	Glass filled polycarbonate

Environmental Specifications

Environmental Space	Outdoor
----------------------------	---------

9-737692-2 | AS-25-Splice-Dry

Packaging and Weights

Included	Base with covers
Packaging quantity	12
Packaging Type	Bag Box