

MC-HR25X-10-12



Three Sector Top Rail Kit, 2-7/8 in OD x 10 ft 6 in face with (12) 2-7/8" Pipe Mounts included

Product Classification

Product Type Co-location platform

General Specifications

Pipe, quantity 0

Sectors, quantity 3

Dimensions

Face Width 3.2 m | 10.5 ft

Platform Width 3,200.4 mm | 126 in

Width 3,200.4 mm | 126 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact steelproducts@commscope.com or call 800-255-1479

Packaging and Weights

Included Corner clips | Hardware | Pipe mounts | Rail

Packaging quantity 1

Weight, net 56.5 kg | 124.561 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

MC-HR25X-10-12

REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code