


# SA-1C

---



PIM-free, stand off adapter that can be strapped to round members for single snap-in hanger attachment

## Product Classification

<b>Product Type</b>	Adapter
<b>Product Brand</b>	PIM-Guard
<b>Ordering Note</b>	CommScope® standard product (Global)

## General Specifications

<b>Adapter Type</b>	Stand-off adapter
<b>Color</b>	Black
<b>Mounting</b>	3/4 in through hole   Round member

## Dimensions

<b>Inside Height</b>	29.21 mm   1.15 in
<b>Outside Width</b>	29.972 mm   1.18 in
<b>Outside Length</b>	34.29 mm   1.35 in

## Material Specifications

<b>Material Type</b>	Engineered plastic
----------------------	--------------------

## Mechanical Specifications

<b>Maximum Loading</b>	Triple stack for hangers SSH-47, SSH-710, SSH-1014, SSH-1416, SSH-411, SSH-1117
<b>Vibration Survival</b>	≥4 hours at resonant frequency

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Environmental Strength Capability</b>	Double cable weight
<b>UV Resistance, minimum with no degradation</b>	≥1000 hours

# SA-1C

---

## Packaging and Weights

<b>Height, packed</b>	17 cm   6.693 in
<b>Width, packed</b>	13 cm   5.118 in
<b>Length, packed</b>	10 cm   3.937 in
<b>Packaging quantity</b>	10
<b>Weight, gross</b>	0.15 kg   0.331 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

