

HFDC-24FIBER



HELIAX® Fiber Distribution Closure 24 fibers - 12 DLCs UPC.

Product Classification

Regional Availability	China EMEA Europe India Latin America Middle East/Africa North America
Portfolio	CommScope®
Product Type	Outdoor junction box
Product Brand	HELIAX®

General Specifications

Application	Used as a fiber junction box
Total Fiber Adapters	12
Color	Black
Doors, quantity	2
Mounting	Pipe, 44–114 mm (1.75–4.5 in) OD Wall
Total Fibers, quantity	24
Total Ports, quantity	12

Dimensions

Height	369.976 mm 14.566 in
Width	213.995 mm 8.425 in
Depth	118.11 mm 4.65 in
Jumper Breakout Length, Maximum	85 mm 3.346 in
Jumper Outlet, Quantity, Maximum	12
Jumper Outlet Diameter, Minimum	0 mm 0 in
Jumper Outlet Diameter, Maximum	7 mm 0.276 in
Trunk Entry, Diameter, Minimum	5.5 mm 0.217 in
Trunk Entry, Diameter, Maximum	17.5 mm 0.689 in
Trunk Entry, Quantity, Maximum	4

HFDC-24FIBER

Material Specifications

Material Type High-impact polycarbonate, UV resistant

Mechanical Specifications

Impact Test Method EN62262 | IEC62262: IK07

Environmental Specifications

Operating Temperature -40 °C to +75 °C (-40 °F to +167 °F)

Qualification Standards IEC 60529, IP68

Packaging and Weights

Included Mounting kit

Weight, net 2.649 kg | 5.84 lb