760242560 | CPP-6A-UDDM-SL-1U-24



Unshielded Discrete Distribution Module Panel, Cat 6A, SL, 1U, 24 port, Black

Product Classification

Regional Availability Australia/New Zealand | Europe

Portfolio CommScope®
Product Type RJ45 patch panel

General Specifications

ANSI/TIA Category 6A

Cable TypeUnshieldedColorBlack

Growth ConfigurationFully loadedPanel StyleStraightRack TypeEIA 19 in

Rack Units 1

Total Ports, quantity 24

Transmission Standards ANSI/TIA-568.2-D | ISO/IEC 11801 Class EA

Dimensions

 Height
 44.45 mm | 1.75 in

 Width
 482.6 mm | 19 in

 Depth, with cable management
 119.38 mm | 4.7 in

Material Specifications

Material Type High-impact, flame retardant, thermoplastic | Powder-coated steel

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$)

Page 1 of 2

760242560 | CPP-6A-UDDM-SL-1U-24

Flammability Rating UL 94 V-0

Safety Standard RCM | UL | cUL

Packaging and Weights

Included Modular jacks (24)

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

