



Ultra High Density 4U modular cassette sliding Panel, accepts (24) G2 modules or MPO panels, providing up to 288 duplex LC ports or up to 192 MPO ports

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel
<b>Product Series</b>	UD

## General Specifications

<b>Application</b>	Accepts twenty-four G2 modular cassettes
<b>Color</b>	Gray
<b>Intelligence Type</b>	iPatch® ready
<b>Interface, front</b>	Unloaded
<b>Rack Units</b>	4
<b>Shelf Movement</b>	Sliding
<b>Total Ports, quantity</b>	0

## Dimensions

<b>Height</b>	177.8 mm   7 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	553.97 mm   21.81 in

## Material Specifications

<b>Material Type</b>	Acrylonitrile butadiene styrene (ABS)   Polycarbonate (PC)   Steel
----------------------	--

## Environmental Specifications

<b>Flammability Rating</b>	UL 94 V-0
----------------------------	-----------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

**Weight, net**

15.966 kg | 35.2 lb

## Regulatory Compliance/Certifications

**Agency**

**Classification**

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

