760193789 | 360-iP-G2-1U-LC-FX



SYSTIMAX 360™ iPatch® G2 LC Fiber Panel, fixed

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber patch panel

Product Brand LazrSPEED® | SYSTIMAX 360™ | iPatch®

Product Series IPATCH

General Specifications

Color Black

Intelligence Type iPatch® enabled

Interface, front LC/UPC

Rack Units 1

Total Ports, quantity 24

Dimensions

 Height
 44.45 mm | 1.75 in

 Width
 482.6 mm | 19 in

 Depth
 323.85 mm | 12.75 in

Material Specifications

Material Type Acrylonitrile butadiene styrene (ABS) | Polycarbonate (PC)

Environmental Specifications

Operating Temperature -5 °C to +50 °C (+23 °F to +122 °F) Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity Up to 95%, non-condensing

Flammability Rating UL 94 V-0

COMMSC PE°

760193789 | 360-iP-G2-1U-LC-FX

Safety Standard ACMA | CE | UL | cUL

Packaging and Weights

Packaging quantity 1

Weight, net 1.814 kg | 4 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

