


CWFMT-277BCOCY1000



FMT MicroVAM Fiber Optic Module, CWDM, 4 channels, mux/demux, SC /UPC, starting wavelength 1571 nm, 1310 nm upgrade port

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	CWDM module
Product Series	FMT

General Specifications

Device Type	Micro VAM
Functionality	Demultiplexing Multiplexing
Access	Front
Application	For use with FMT panels For use with NGF frames
Circuits, quantity	1
Distribution Type	4-channel CWDM
Interface, front	SC/UPC
Interface, Input	SC/UPC
Interface, Output	SC/UPC
Multiplexers, quantity	1
Port Type, optional	Upgrade port

Dimensions

Height	71.88 mm 2.83 in
Width	17.27 mm 0.68 in
Depth	177.8 mm 7 in

Optical Specifications

Starting Wavelength	1571 nm
----------------------------	---------

CWFMT-277BCOCY1000

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

