FPP-12SU-180M



HELIAX® Fiber Plug and Play 6 RRU Solution that will interface with Ericsson, Nokia, Huawei or ZTE RRU's, 180M

Product Classification


Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Outdoor junction box
Product Brand	HELIAX®
General Specifications	
Application	For use with Ericsson, Nokia, Huawei or ZTE remote radio units (RRU's)
Cable Entry Location	Side
Cable Entry, quantity, maximum, right	3
Cable Entry, quantity, maximum, top	3
Color	Gray
Mounting	Pipe, 76.2–101.6 mm (3.0–4.0 in) OD Wall
Dimensions	
Height	406.4 mm 16 in
Width	406.4 mm 16 in
Depth	234.95 mm 9.25 in

Outline Drawing

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 21, 2023





Material Specifications

Material Type

Aluminum

Environmental Specifications

Environmental Space

Qualification Standards

Indoor | Outdoor IEC 60529:2001, IP67

Packaging and Weights

Included

Weight, net

Mounting kit 11.299 kg | 24.91 lb

Regulatory Compliance/Certifications

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 21, 2023



FPP-12SU-180M

Agency

CHINA-ROHS ISO 9001:2015

REACH-SVHC

ROHS

UK-ROHS



Below maximum concentration value Designed, manufactured and/or distributed under this quality management system Compliant as per SVHC revision on www.commscope.com/ProductCompliance Compliant Compliant

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 21, 2023

