

C100-SMSM-12

CNT-100 CNT® Jumper with interface types SMA Male and SMA Male,
12 ft



Product Classification

Product Type	Braided cable assembly
Product Brand	CNT®
Product Series	CNT-100

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	CNT-100
Interface, Connector A	SMA Male
Interface, Connector B	SMA Male
Specification Sheet Revision Level	A

Dimensions

Length	3.658 m 12.001 ft
Nominal Size	0.100 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.433	14.99

Jumper Assembly Sample Label

C100-SMSM-12



Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

Included Products

100PSM-CR

– SMA Male for CNT-100 braided cable

CNT-100-FR

– CNT-100-FR, CNT[®] 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket