

7643288-01 | SR 8/POI w/o guiderails

ION® Active Intelligent Point of Interface Subrack for ION-U Applications



Product Classification

Product Type	Point of interface subrack
Product Brand	ION®

General Specifications

General Alarm	Integrated into management system
Interface Slots Available, quantity	1
Mounting	Rack
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
Rack Type	EIA 19 in
Slots Available, quantity	8

Dimensions

Height	177 mm 6.969 in
Width	483 mm 19.016 in
Depth	462 mm 18.189 in

Electrical Specifications

Electrical Safety Standard	EN 60950
Power Consumption	276 W
Voltage Range	+10 to +14 Vdc

Environmental Specifications

Operating Temperature	+5 °C to +50 °C (+41 °F to +122 °F)
------------------------------	-------------------------------------

7643288-01 | SR 8/POI w/o guiderails

Storage Temperature	-25 °C to +70 °C (-13 °F to +158 °F)
Relative Humidity	46%–94%
Mean Time Between Failures (MTBF) at Temperature	213,000 h @ 25 °C

Packaging and Weights

Height, packed	570 mm 22.441 in
Width, packed	305 mm 12.008 in
Depth, packed	620 mm 24.409 in
Weight, gross	11.6 kg 25.574 lb
Weight, net	8 kg 17.637 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system