
FE-18184



Product Classification

HELIAX® Outdoor Excess Cable Enclosure, 18 in x 18 in x 4 in

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Outdoor junction box
Product Brand	HELIAX®
General Specifications	
Application	Accepts 30 m of excess fiber trunk cable
Cable Entry, quantity, maximum, left	1
Cable Entry, quantity, maximum, right	1
Color	Gray
Mounting	Pipe, 76.2 mm (3 in) OD Wall
Dimensions	
Height	465.582 mm 18.33 in
Width	457.2 mm 18 in
Depth	101.6 mm 4 in
Material Specifications	
Material Type	Aluminum
Environmental Specifications	
Environmental Space	Indoor Outdoor
Qualification Standards	IEC 60529:2001, IP64
Packaging and Weights	
Included	Mounting kit
Weight, net	4.463 kg 9.84 lb
	Р

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 21, 2023



COMMSCOPE°

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 21, 2023

