

# 406042-1 | RCM-RM-2'

---

Rear Cable Management, rack mountable, 2 inch



## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Cable management hardware

## General Specifications

<b>Color</b>	Black
<b>Rack Type</b>	EIA 19 in

## Dimensions

<b>Height</b>	11.938 mm   0.47 in
<b>Width</b>	459.232 mm   18.08 in
<b>Depth</b>	64.008 mm   2.52 in

## Material Specifications

<b>Finish</b>	Powder-coated, textured
<b>Material Type</b>	Aluminum

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	UL   cUL

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

# 406042-1 | RCM-RM-2'

---

CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

