T-10-UW-43-M



Termination Load, 0–6000 MHz, Not for PIM-rated applications

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Termination Load

General Specifications

Device TypeTermination LoadApplicationIndoor/Outdoor

Color Black
Inner Contact Plating Silver

Interface 4.3-10 Male

Outer Contact Plating Trimetal

Dimensions

 Length
 53 mm | 2.087 in

 Diameter, maximum
 35 mm | 1.378 in

Electrical Specifications

Average Power, maximum 10 W Impedance 50 ohm

Operating Frequency Band 0 - 6000 MHz

VSWR 1.15

Environmental Specifications

Operating Temperature $-35 \,^{\circ}\text{C} \text{ to } +50 \,^{\circ}\text{C} \, (-31 \,^{\circ}\text{F to } +122 \,^{\circ}\text{F})$

Relative Humidity Up to 100%

Ingress Protection Test Method IEC 60529:2001, IP65

Packaging and Weights

COMMSCOPE®

T-10-UW-43-M

 Height, packed
 53 mm | 2.087 in

 Width, packed
 58 mm | 2.283 in

 Length, packed
 68 mm | 2.677 in

 Weight, gross
 0.16 kg | 0.353 lb

 Weight, net
 0.13 kg | 0.287 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

