

BB-S10-10



Welded Pipe-to-Pipe Clamp, heavy duty, joins two 1-1/2 in to 3-1/2 in OD round members

Product Classification

Product Type Clamp set

General Specifications

Mounting Pipe-to-pipe

Taper Taper Non-tapered

Dimensions

Height 50.8 mm | 2 in

Width 152.4 mm | 6 in

Length 254 mm | 10 in

Mounting Diameter, maximum 88.9 mm | 3.5 in

Mounting Diameter, minimum 38.1 mm | 1.5 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Clamp halves | Threaded rod

Packaging quantity 2

Weight, net 5.9 kg | 13.007 lb

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--------------------------------------------------------------------------------|
| CHINA-ROHS | Above maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

