

SCPTW



Small Cell Antenna Pole Top Mount with 37" Standoff (for Poles 8in to 10in OD)

Product Classification

Product Type Pole mount kit | Wood pole mount

General Specifications

Mounting Wood pole

Dimensions

Height 1,046.48 mm | 41.2 in

Width 254 mm | 10 in

Length 254 mm | 10 in

Mounting Diameter, maximum 254 mm | 10 in

Mounting Diameter, minimum 203.2 mm | 8 in

Stand-off Distance 939.8 mm | 37 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact steelproducts@commscope.com or call 800-255-1479

Packaging and Weights

Included Attachment hardware | Universal Small Cell Antenna Bracket – see drawing for compatible models

Packaging quantity 1

Regulatory Compliance/Certifications

SCPTW

Agency

CHINA-ROHS

ISO 9001:2015

ROHS

UK-ROHS

**Classification**

Above maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant/Exempted

Compliant/Exempted

*** Footnotes****Wind Rating**

BWS—Base Wind Speed; FBC—Florida Building Code