


BUDI-R24JC0919A | BUDI-R24JC0919A



BUDI™ Rapid Terminal, 24-position, SC/APC, Indoor/Outdoor riser cable, MPO at far end, 300 ft

- Designed to provide a quick and simple solution for installing fiber in small and medium sized MDU's
- Incorporates a unique fiber cable spooling system that stores up fiber cable within the enclosure
- Removes the need for field termination and extensive site survey inspections

Product Classification

Regional Availability	Australia/New Zealand Europe North America
Portfolio	CommScope®
Product Type	Rapid distribution terminal
Product Brand	BUDI™ RapidReel®
Product Series	BUDI-R
Warranty	For more information, please consult our Product Warranty guidelines

General Specifications

Functionality	Patching Slack storage
Adapters, quantity	24
Cable Entry Location	Bottom
Cable Sealing Type	Gasket/grommet configuration
Cable Type	Indoor/outdoor - Stranded
Color	Gray
Distribution Type	24 ports
Interface	SC/APC
Interface, stub	MPO
Lock Type	Security screw
Mounting	Wall mount
Port, quantity	24

Dimensions

Height	270 mm 10.63 in
Width	214 mm 8.425 in

BUDI-R24JC0919A | BUDI-R24JC0919A

Depth	125 mm 4.921 in
Cable Length	91 m 298.556 ft
Enclosure Size	Small

Material Specifications

Material Type	Polycarbonate ABS (PC-ABS)
----------------------	----------------------------

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2

Environmental Specifications

Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Environmental Space	Indoor/Outdoor
Flammability Rating	UL 94 V-0
Qualification Standards	IEC 61753-1 UL

Packaging and Weights

Packaging quantity	1
Packaging Type	Carton

* Footnotes

Warranty	For more information, please consult our Product Warranty guidelines
-----------------	--