## FPX-24MPRDA6

# FPX Fiber Optic MPO Module, Multimode Ultra 50/125 (OM3), 12 fiber LC adapter, right, putty white

- FPX modules offer the end-user the flexibility of a plug-and-play MPO architecture with a "grow as you go" approach to the network
- Each module has a front bulkhead identical to the adapter pack with an internal cable assembly converting to an MPO male connector
- All fiber connectivity is housed in an enclosed module with a rear MPO adapter allowing the user to utilize an MPO trunk to turn up service

#### Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Fiber module
Product Series	FPX

#### General Specifications

Functionality	Breakout
Application	For use with FPX panels
Adapter Color	Blue
Adapters, quantity, front	12
Adapters, quantity, rear	2
Body Style	Duplex   Right orientation
Color, front	Putty white
Color, housing	Putty white
Color, rear	Putty white
Interface, front	LC/UPC
Interface, rear	MPO
Interface Feature, rear	Standard
Polarity	Pairs, straight
Total Ports, quantity, front	24
Dimensions	
Height	33.02 mm   1.3 in
Width	176.53 mm   6.95 in

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024




## FPX-24MPRDA6

#### Depth

127 mm | 5 in

### Ordering Tree



<sup>1</sup> SC only <sup>2</sup> LC only

#### **Optical Specifications**

Fiber Mode	Multimode
Fiber Type	OM3

#### **Environmental Specifications**

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)

#### Packaging and Weights

Packaging quantity	1		
Packaging Type	Bag	Ι	Carton

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024



### FPX-24MPRDA6

TL 9000:2016 (R6)

UK-ROHS

Compliant to this quality management practice

Compliant

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024

