



Unshielded Modular Panel, M-series, 1U, 24 port, Black

Product Classification

Regional Availability	Asia Australia/New Zealand Latin America North America
Portfolio	CommScope®
Product Type	RJ45 patch panel
Product Series	M Series

General Specifications

Cable Type	Unshielded
Color	Black
Intelligence Type	Passive
Rack Type	EIA 19 in
Rack Units	1
Total Ports, quantity	24

Dimensions

Height	43.69 mm 1.72 in
Width	482.6 mm 19 in
Depth	105.92 mm 4.17 in

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic Powder-coated steel
----------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Flammability Rating	UL 94 V-0
Safety Standard	UL cUL

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

