760209940 | HD-1U



High Density 1U modular cassette sliding Panel, accepts (4) G2 modules or MPO panels, providing up to 48 duplex LC ports, or up to 32 MPO ports

Product Classification

| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
|-----------------------|---|
| Portfolio | CommScope® |
| Product Type | Fiber patch panel |
| Product Series | HD |

General Specifications

| Application | Accepts four G2 modular cassettes |
|-----------------------|-----------------------------------|
| Color | Black + Silver gray (front) |
| Intelligence Type | iPatch® ready |
| Interface, front | Unloaded |
| Rack Type | EIA 19 in |
| Rack Units | 1 |
| Shelf Movement | Sliding |
| Total Ports, quantity | 0 |
| | |

Dimensions

| Height | 44.45 mm 1.75 in |
|--------|----------------------|
| Width | 482.6 mm 19 in |
| Depth | 541.78 mm 21.33 in |

Material Specifications

Material Type

Steel

Environmental Specifications

| Flammability Rating | UL 94 V-0 |
|---------------------|-----------|
| Safety Standard | UL 1863 |

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024



760209940 | HD-1U

Packaging and Weights

Packaging quantity

Weight, net 5.625 kg | 12.4 lb

1

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |
| | |

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024

