

# 760210732 | HD-1U-FX

---



High Density 1U modular cassette fixed Panel, accepts (4) G2 modules or MPO panels, providing up to 48 duplex LC ports, or up to 32 MPO ports

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel
<b>Product Series</b>	HD

## General Specifications

<b>Application</b>	Accepts four G2 modular cassettes
<b>Color</b>	Black + Silver gray (front)
<b>Intelligence Type</b>	iPatch® ready
<b>Interface, front</b>	Unloaded
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	1
<b>Shelf Movement</b>	Fixed
<b>Total Ports, quantity</b>	0

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	458.98 mm   18.07 in

## Material Specifications

<b>Material Type</b>	Steel
----------------------	-------

## Environmental Specifications

<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	UL 1863

## Packaging and Weights

**Packaging quantity** 1  
**Weight, net** 4.082 kg | 9 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

