

760118323 | M2400-1U-GS



M2400 1U Modular Panel, 24 port (MGS600 / MGS400 / UNJ10GT), Black

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio

CommScope®

Product Type

RJ45 patch panel

Product Brand

GigaSPEED X10D®

Product Series

M Series

General Specifications

ANSI/TIA Category

6 | 6A

Cable Type

Unshielded

Color

Black

Intelligence Type

Passive

Rack Type

EIA 19 in

Rack Units

1

Total Ports, quantity

24

Dimensions

Height

43.69 mm | 1.72 in

Width

482.6 mm | 19 in

Depth

53.59 mm | 2.11 in

Compatible Diameter Over Dielectric, maximum

1.168 mm | 0.046 in

Compatible Diameter Over Dielectric, minimum

0.762 mm | 0.03 in

Material Specifications

Material Type

High-impact, flame retardant, thermoplastic | Powder-coated steel

Environmental Specifications

760118323 | M2400-1U-GS

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	UL cUL

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

