760201145 | 360-iP-1100-E-GS6-1U-24



SYSTIMAX 360™ iPatch® 1100GS6 Evolve U/UTP Patch Panel, 24 port

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	RJ45 patch panel
Product Brand	SYSTIMAX 360™ iPatch®
General Specifications	
ANSI/TIA Category	6A
Cable Type	Unshielded
Color	Silver
Intelligence Type	iPatch® enabled
Panel Style	Straight
Rack Units	1
Total Ports, quantity	24
Wiring	T568A T568B
Dimensions	
Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	206.5 mm 8.13 in
Compatible Diameter Over Dielectric, maximum	1.168 mm 0.046 in
Electrical Specifications	
Current Rating at Temperature	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1,500 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 1, 2024



760201145 | 360-iP-1100-E-GS6-1U-24

Mechanical Specifications

Plug Insertion Life, minimum	750 times
Environmental Specifications	
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Safety Standard	UL cUL
Packaging and Weights	
Packaging quantity	1
Regulatory Compliance/Certifications	

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 1, 2024

