

760202648 | 360-iP-UP-KIT-AE-48



SYSTIMAX 360™ iPatch® Upgrade Kit for Evolve Angled Panel, 48 Port, 5 pack

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio

SYSTIMAX®

Product Type

RJ45 patch panel

Product Brand

SYSTIMAX 360™ | iPatch®

General Specifications

ANSI/TIA Category

6 | 6A

Color

Cool gray

Intelligence Type

iPatch® upgrade kit

Panel Style

Angled

Total Ports, quantity

48

Dimensions

Compatible Diameter Over Dielectric, maximum

1.168 mm | 0.046 in

Compatible Diameter Over Dielectric, minimum

0.762 mm | 0.03 in

Electrical Specifications

Current Rating at Temperature

1.5 A @ 20 °C | 1.5 A @ 68 °F

Dielectric Withstand Voltage, RMS, conductive surface

1,500 Vac @ 60 Hz

Dielectric Withstand Voltage, RMS, contact-to-contact

1,000 Vac @ 60 Hz

Material Specifications

Material Type

Acrylonitrile butadiene styrene (ABS) | Polycarbonate

Environmental Specifications

Operating Temperature

-5 °C to +50 °C (+23 °F to +122 °F)

760202648 | 360-iP-UP-KIT-AE-48

| | |
|----------------------------|--------------------------------------|
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Relative Humidity | Up to 95%, non-condensing |
| Flammability Rating | UL 94 V-0 |
| Safety Standard | ACMA CE UL cUL |

Packaging and Weights

| | |
|---------------------------|--------------------|
| Packaging quantity | 5 |
| Weight, net | 0.113 kg 0.25 lb |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Above maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

