760239075 | UDS-2U-WH-LC-A-ULL



UDS 2RU splice panel, 144 duplex LC/UPC ports, Method A, ULL

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber patch/splice panel

Product Series UDS

General Specifications

Application Preloaded with 12 UDS modules

Color White

Intelligence Type Not iPatch® ready

Interface, front LC/UPC

Pigtail Assembly Type 12-fiber, ribbon

Pigtails Included, quantity 12

Rack Type EIA 19 in

Rack Units 2

Shelf Movement Sliding

Splice Trays Included, quantity 4

Total Ports, quantity 144

Dimensions

 Height
 88.9 mm | 3.5 in

 Width
 444.5 mm | 17.5 in

 Depth
 609.6 mm | 24 in

Optical Specifications

Insertion Loss, maximum 0.25 dB



760239075 | UDS-2U-WH-LC-A-ULL

Environmental Specifications

Safety Standard cUL US 1863

Packaging and Weights

Packaging quantity

Weight, net 6.804 kg | 15 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

