760242725 | SD-4U-SPLICE

Fiber splice panel



SD 4U Splicing fiber Panel, accepts up to 6, 288f FOST Splice Trays, providing up to 1728 fiber mass fusion splicing and 288 single fiber splicing

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Series SD

General Specifications

Color Black

Interface, front Unloaded

Rack Units 4

Shelf Movement Sliding

Total Ports, quantity 0

Dimensions

Product Type

 Height
 177.8 mm | 7 in

 Width
 482.6 mm | 19 in

 Depth
 485.14 mm | 19.1 in

Environmental Specifications

Flammability Rating UL 94 V-0

Packaging and Weights

Weight, net 6.35 kg | 14 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

COMMSCOPE®