FL2-S2702A095-AU00



FL2000 Fiber Termination Panel, 24 SC/UPC, singlemode, 2RU, 19 in, putty white, pre-terminated with IFC cable, 95 meters, Stub tail at far end

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch panel, with IFC cable

Product Series FL2000

General Specifications

Functionality Patching

Adapter Packs Included, quantity 4

 Cable Exit Location
 Upward

 Cable Stub Type
 IFC

Color Putty white

Growth Configuration Fully loaded

Interface, frontSC/UPCInterface, rearStub tail

Rack Type EIA 19 in

Rack Units 2

Shelf MovementHingedSplicing Capacity, maximum0

Total Ports, quantity 24

Dimensions

Cable Length

 Height
 88.9 mm | 3.5 in

 Width
 482.6 mm | 19 in


 Depth
 256.54 mm | 10.1 in

COMMSC PE®

95 m | 311.68 ft

FL2-S2702A095-AU00

Ordering Tree



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Storage Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights



FL2-S2702A095-AU00

Packaging quantity

1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed un

ınder this quality management system REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted Compliant/Exempted **UK-ROHS**

