

7640450-00



ION® Alarm Cable for Active Intelligent Point of Interface, 0.7 m inter-subrack connection

Product Classification

Product Type Alarm cable

Product Brand ION®

General Specifications

Cable, quantity 4

Connector A Crimped dc connector, female, 4 contacts

Connector B Crimped connector, female, 4 contacts

Note Detailed Product Specifications are available. Please contact your local CommScope representative.

Dimensions

Height 200 mm | 7.874 in

Width 10 mm | 0.394 in

Depth 250 mm | 9.843 in

Cable Gauge 24 AWG

Electrical Specifications

Current per Pin 0.5 A

Electrical Safety Standard EN 60950

Voltage Range +5 to +60 Vdc

Packaging and Weights

Height, packed 250 mm | 9.843 in

Width, packed 20 mm | 0.787 in

Depth, packed 300 mm | 11.811 in

7640450-00

Weight, gross 0.5 kg | 1.102 lb

Weight, net 0.25 kg | 0.551 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015



Classification

Designed, manufactured and/or distributed under this quality management system