

# OG3LX6-L-CS1-HC

---



HELIAX®, LC Loopback, Multimode

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber loopback
<b>Product Brand</b>	HELIAX®

## General Specifications

<b>Interface</b>	LC/UPC
------------------	--------

## Mechanical Specifications

<b>Mating Durability, maximum</b>	0.5 dB @ 500 cycles
-----------------------------------	---------------------

## Optical Specifications

<b>Insertion Loss, maximum</b>	1 dB
--------------------------------	------

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +80 °C (-40 °F to +176 °F)
------------------------------	--------------------------------------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted

# OG3LX6-L-CS1-HC

---

UK-ROHS

Compliant/Exempted

