

E20® Empty Conduit, 8.5 mm/6 mm, plenum, opaque white



- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	North America
Product Type	Empty conduit
Product Brand	E#O®
Government Funding	Build America Buy America (BABA) compliant*
Warranty	One year

General Specifications

Color	Opaque white
Conduit Type	Non-toneable
Density, maximum	0.955 g/cm ³ 0.035 lb/in ³
Density, minimum	0.941 g/cm ³ 0.034 lb/in ³
Design Standard	ASTM D3350-05
Wall Type	Smooth

Dimensions

Length	762 m 2500 ft
Inner Diameter, nominal	6.096 mm 0.24 in
Outer Diameter, nominal	8.509 mm 0.335 in
Wall Thickness, minimum	1.143 mm 0.045 in
Nominal Size	8.5 mm

Material Specifications

Material Type	PVDF
----------------------	------

Mechanical Specifications

360000017

Minimum Bend Radius, unsupported	330.2 mm 13 in
Tensile Strength at yield, minimum	20.684 N/mm ² 3000 psi
Pulling Tension, maximum	80.286 kg 177 lb

Packaging and Weights

Weight, net	0 kg/km 0 lb/kft
--------------------	--------------------

Regulatory Compliance/Certifications

Agency

ISO 9001:2015



Classification

Designed, manufactured and/or distributed under this quality management system

* Footnotes

Warranty

For more information, please consult our Product Warranty guidelines