



Fiber Optic Patch Cord, Simplex, 0.9mm,OM4, SC/UPC to SC/UPC, AQUA

Product Classification

Regional Availability	Asia Australia/New Zealand China India
Portfolio	CommScope®
Product Type	Fiber patch cord, simplex

General Specifications

Connector A, quantity	1
Color, boot A	Aqua
Color, connector A	Black
Connector B, quantity	1
Color, boot B	Aqua
Color, connector B	Black
Interface, Connector A	SC/UPC
Interface, Connector B	SC/UPC
Jacket Color	Aqua
Total Fibers, quantity	1

Dimensions

Cable Assembly Length Range (m)	1 – 999
Cable Assembly Length Range (ft)	1 – 999
Diameter Over Jacket	0.9 mm 0.035 in

Mechanical Specifications

Cable Retention Strength, maximum	1.00 lb @ 0° 1.00 lb @ 90°
--	------------------------------

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM4, LazrSPEED®
Insertion Loss, maximum	0.3 dB

2105086

Return Loss, minimum 27 dB

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Low Smoke Zero Halogen (LSZH)

Packaging and Weights

Packaging quantity 1