221213



Weatherproofing Kit for Connectors and Splices, includes butyl rubber and PVC tape

Product Classification

Product Type Weatherproofing tape

Ordering Note CommScope® standard product (Global)

General Specifications

Application Provides additional moisture seal for cable connections

Applications per Kit Four 1/2 in-7/8 in | Twelve 1/2 in-1/2 in | Twelve 1/2 in-7/8 in to

device | Two 1/2 in-2-1/4 in

Harmonized System (HS) Code 4005.91.0000 (Compounded Rubber, Unvulcanized in Plates, Sheets and

Strip)

Dimensions

Nominal Size 1-1/4 in | 1-5/8 in | 1/2 in | 1/4 in | 2-1/4 in | 3/8 in | 5/8 in | 7

/8 in

Material Specifications

Material Type Butyl rubber tape | PVC tape

Environmental Specifications

UV Resistance Test MethodButyl test method in QUV weatherometer cycle of 8 hours UV at 150 °F then 4

hours of condensation at 104 °F | PVC tape test method UL 510, ASTM

D1000

UV Resistance, minimum with no degradation ≥1000 hours

Weather Resistance Test Method 04AS00-03.6.0 | MIL-STD-1344A, Method 1002

Packaging and Weights

 Height, packed
 195.58 mm | 7.7 in

 Width, packed
 175.26 mm | 6.9 in

 Length, packed
 96.52 mm | 3.8 in

Page 1 of 2

221213

Included One roll of 2 in PVC tape | Six rolls of 2-1/2 in butyl rubber tape | Two

rolls of 3/4 in PVC tape

Packaging quantity

Weight, gross 1.52 kg | 3.351 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

42615-10 - Butyl Rubber Tape, 24 in 9905-41 - Black 3/4 in PVC Tape, 66 ft 9905-71 - Black 2 in PVC Tape, 20 ft