


838541-000 | FOSC-OC-3CDX471NN

FOSC® D-TRAY-72 type, CWDM, 8 channels + upgrade port + 1310 nm port, double demux, 20 nm channel spacing, 1539.77 nm starting wavelength



Product Classification

Regional Availability	North America
Product Type	CWDM splice tray
Product Brand	FOSC®
Product Series	FOSC-OC

General Specifications

Application	For use in FOSC closures
Interface, Input	Stub tail
Interface, Output	Stub tail

Dimensions

Height	375.92 mm 14.8 in
Width	152.4 mm 6 in
Depth	10.67 mm 0.42 in

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

