


204673-24



24 Port Entrance Panel, 4 x 6

Product Classification

Product Type	Entrance panel
Ordering Note	CommScope® non-standard product

General Specifications

Color	Gray
Entry Panel Port Size	101.6 mm 4 in
Number of Ports	24
Panel Type	Multiple

Dimensions

Height	787.4 mm 31 in
Width	1,003.3 mm 39.5 in

Material Specifications

Material Type	Aluminum
----------------------	----------

Environmental Specifications

Weather Resistance Test Method	04AS00-03.9.0 IEC 60529:2001, IP66
---------------------------------------	--------------------------------------

Packaging and Weights

Height, packed	668.02 mm 26.3 in
Width, packed	459.74 mm 18.1 in
Length, packed	50.8 mm 2 in
Included	Entry cap Hardware Port
Packaging quantity	1
Weight, gross	2.5 kg 5.512 lb

204673-24

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

Included Products

CAP-4 – Snap-in Entry Port Cap, 4 in

CAP-4



Snap-in Entry Port Cap, 4 in

Product Classification

Product Type	Port cap
Ordering Note	CommScope® non-standard product

General Specifications

Color	Black
Entry Panel Port Size	101.6 mm 4 in
Panel Type	Multiple

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Packaging and Weights

Height, packed	127 mm 5 in
Width, packed	127 mm 5 in
Length, packed	248.92 mm 9.8 in
Included	Entry cap
Packaging quantity	1
Weight, gross	0.02 kg 0.044 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant
UK-ROHS	Compliant

