

L7CLICK



Double Click-on Hanger for 1-5/8 in coaxial cable

Product Classification

Product Type	Hanger kit
Ordering Note	CommScope® non-standard product

General Specifications

Cables per Hanger	1
Color	Black
Hanger Type	Click-on hanger
Mounting	3/8 in (M10) drilled cable ladder

Dimensions

Maximum Stack Height	3
Height	51.1 mm 2.012 in
Width	79.5 mm 3.13 in
Length	154.7 mm 6.091 in
Compatible Cable Diameter Range	49–51.1 mm
Compatible Diameter, maximum	51.1 mm 2.012 in
Compatible Diameter, minimum	49 mm 1.929 in
Nominal Size	1-5/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

L7CLICK

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 12.9 cm | 5.079 in

Width, packed 5.5 cm | 2.165 in

Length, packed 5.9 cm | 2.323 in

Packaging quantity 10

Weight, gross 1.6 kg | 3.527 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power