

SnapSeal™ Entry Cushion with 6 holes for 1/4 in corrugated coaxial cable



Product Classification

Product Type	Entry cushion
Ordering Note	CommScope® non-standard product

General Specifications

Cable Type	Corrugated
Cables per Cushion	6
Color	Black

Dimensions

Height	101.6 mm 4 in
Length	31.75 mm 1.25 in
Nominal Size	1/4 in

Material Specifications

Material Type	Thermoplastic elastomer (TPE)
----------------------	-------------------------------

Environmental Specifications

UV Resistance Test Method	MIL-STD-810E, Procedure 11, Method 505
UV Resistance, minimum with no degradation	≥1000 hours
Weather Resistance Test Method	04AS00-03.9.0

Packaging and Weights

Height, packed	170.18 mm 6.7 in
Width, packed	129.54 mm 5.1 in

SEC-614

Length, packed	99.06 mm 3.9 in
Included	Compression ring SnapSeal™ entry cushion
Packaging quantity	1
Weight, gross	0.8 kg 1.764 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant