

SM-UT1012



Universal Angle Saddle Mount, 12 in triangular legs and 10 in to 12 in angle members

Product Classification

Product Type Saddle mount

General Specifications

Mounting Angle members, 254–304.8 mm (10–12 in) | Triangular legs, 304.8 mm (12 in)

Tower Taper Non-tapered

Dimensions

Height 203.2 mm | 8 in

Width 406.4 mm | 16 in

Length 304.8 mm | 12 in

Mounting Diameter, maximum 304.8 mm | 12 in

Mounting Diameter, minimum 0 mm | 0 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Mount

Packaging quantity 2

Weight, net 36.3 kg | 80.028 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system