

TW-78-EZFC



Torque Wrench for 7/8 in EZfit® connectors, 34 mm

Product Classification

Product Type	Wrench
Ordering Note	CommScope® non-standard product

General Specifications

Application	Attaches connectors to coaxial cable
Calibration	6 mo
Tool Type	Torque wrench

Dimensions

Wrench Opening	34.036 mm 1.34 in
-----------------------	---------------------

Material Specifications

Material Type	Steel
----------------------	-------

Mechanical Specifications

Torque Tolerance	+5/-0
Torque Value	300.93 in lb 34.001 N-m

Packaging and Weights

Height, packed	299.72 mm 11.8 in
Width, packed	299.72 mm 11.8 in
Length, packed	106.68 mm 4.2 in
Packaging quantity	1
Weight, gross	2.19 kg 4.828 lb

Regulatory Compliance/Certifications

Agency	Classification
---------------	-----------------------

TW-78-EZFC

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

