


XA-2030



Crossover Angle, 2.38 in to 2.88 in OD

Product Classification

Product Type Mounting kit

General Specifications

Tower Taper Non-tapered

Dimensions

Height 152.4 mm | 6 in

Width 152.4 mm | 6 in

Length 152.4 mm | 6 in

Mounting Diameter, maximum 73.66 mm | 2.9 in

Mounting Diameter, minimum 60.96 mm | 2.4 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Angle | U-bolts

Packaging quantity 2

Weight, net 1.8 kg | 3.968 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

XA-2030

