CMAX-LHM2-3030-153



Low PIM Directional High Capacity Venue 2x2 MIMO Antenna 4G/5G/C-Band, 617–960 MHz, 1695–2700 MHz and 3300-4200MHz, 4.3-10

Product Classification

Product Type Over-the-head stadium antenna

General Specifications

Application Indoor/Outdoor

Antenna Type Directional

Antenna Array Characteristic MIMO 2x2

Polarization ±45°

Color White (RAL 9016)

Number of Ports 2

Radome Material Fiberglass, UV resistant

RF Connector Interface 4.3-10 Female

Dimensions

 Width
 750 mm | 29.528 in

 Depth
 120 mm | 4.724 in

 Length
 750 mm | 29.528 in

Electrical Specifications

Impedance50 ohmLightning Protectionde Ground

Operating Frequency Band 1710 – 2200 MHz | 2200 – 2700 MHz | 3300 – 4200 MHz | 617 – 698 MHz | 698

– 960 MHz

Electrical Note Values typical, unless otherwise stated

Electrical Specifications

Frequency Band, MHz 617-698 698-960 1695-2200 2200-2700 3300-4200

Gain, dBi 12 13.5 12.5 14 14.5

COMMSCOPE®

CMAX-LHM2-3030-153

Beamwidth, Horizontal, degrees	41	34	40	32	27
Beamwidth, Vertical, degrees	44	35	37	30	28
Horizontal Sidelobe, dB	18	18	18	18	18
Front-to-Back Ratio, Copolarization 180° ± 30°, dB	25	25	30	30	25
Isolation, Cross Polarization, dB	25	25	22	22	20
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153	-153	-153
Input Power per Port, maximum, watts	200	200	200	200	200

Mechanical Specifications

Wind Loading @ Velocity, maximum 1,826.0 N @ 241 km/h (410.5 lbf @ 150 mph)

Wind Speed, maximum 241.4 km/h (150 mph)

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Relative Humidity Up to 100%

Ingress Protection Test Method IEC 60529:2001, IP65

Vibration Test Method ASTM D4169 | IEC 60068-2-6

Packaging and Weights

 Width, packed
 805 mm | 31.693 in

 Depth, packed
 218 mm | 8.583 in

 Length, packed
 1012 mm | 39.843 in

 Included
 Mounting bracket

Net Weight, with mounting kit 15.8 kg | 34.833 lb

Packaging quantity 1

 Weight, gross
 19.8 kg | 43.651 lb

 Weight, net
 13 kg | 28.66 lb

