



Constellation™ Transmitter Power Module, 3 kW module that provides the CPCX-12 with up to 12 kW of capacity

Product Classification

Regional Availability	North America
Portfolio	SYSTIMAX®
Product Type	Power supply
Product Brand	Constellation™

General Specifications

Color	Putty white
Standards	CISPR 32 IEC/EN 55032 EN 300 386 v2.1.1 EN 50121-4 FCC Part 15B Class A

Dimensions

Height	41.5 mm 1.634 in
Width	109 mm 4.291 in
Depth	327 mm 12.874 in
Length	327 mm 12.874 in

Electrical Specifications

Output Current, maximum	9 A
Output Voltage	336 Vdc

Material Specifications

Material Type	Powder coated steel
----------------------	---------------------

Environmental Specifications

Operating Temperature	-20 °C to +50 °C (-4 °F to +122 °F)
Storage Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Relative Humidity	5%–95%, non-condensing
Environmental Space	Indoor

Safety Standard IEC 62368-1

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

